


Arteor™ with Netatmo

Connected wireless control for roller shutters and orientable sun shades

Cat. Nos: 5 742 62/82



1. USE


Zone or centralised control for wired roller shutters and orientable sun shades switches.

- Fixes directly on the wall or screws onto a flush-mounting box.
 - Multi-gang versions can be combined with other wiring accessories.
 - Fits on a piece of furniture (movable).
- Can control up to 20 roller shutters switches.

2. RANGE

Description	White	Magnesium
Connected wireless control for roller shutters and orientable sun shades (OSS). Supplied with battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Support frame and repositionable self-adhesive fixings supplied. To be equipped with plate.	5 742 62	5 742 82



3. DIMENSIONS (mm)



A	B	C
56	56	10.5

5. OPERATION

Integrated time delay for up/down inversion: 500 ms



Arteor™ with Netatmo

Connected wireless control for roller shutters and orientable sun shades

6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Protection against impacts: IK 04

Protection against solid bodies/liquids: IP 20

■ 6.2 Material characteristics

Rocker plate: ABS White RAL 9003

ABS Magnesium painted

Mechanism casing: PC

Halogen-free

UV-resistant

Self-extinguishing: 650°C/30 s

■ 6.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)

Battery life: 8 years for 10 activations a day

ZigBee radio technology

Frequency: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

■ 6.4 Climate characteristics

Storage temperature: 0°C to + 45°C

Usage temperature: +5°C to + 35°C

7. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:

Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.



Take care to recycle the battery appropriately

Caution: Always test before using special cleaning products.

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e-catalogue.

The undersigned, LEGRAND, declares that the radio-electric equipment type (5 742 62/82) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com